



Unit #:
XX-XXXX

DEALER: XYZ Dealer
CUSTOMER: XYZ Emergency Ambulance
 Street or P.O. Box _____
 City, State, Zip _____
 Customer Contact: _____
 Sales Associate: _____
VIN#: *To be assigned by MEDIX*

| | | |
|-------------------------|-------------------|---|
| Chassis Model Yr | | 2017 |
| MEDIX Model | | SRH-148, Type II |
| CHASSIS | | Ford 250 MR Van, 3.2L I5 Diesel, 148"WB, 9000 GVWR |
| BODY | | OEM Van Body w/Mid-High Roof |
| QTY | STD/OPT | Description |
| 1 | 15-2000-TD | Chassis & Conversion |
| | | |
| | 01- | Flooring & Interior Colors |
| 1 | STD | Cabinets: (Specify Color) Color: STAINLESS STEEL |
| 1 | STD | Upholstery: (Specify Color) Color: _____ Brand: EVS |
| 1 | STD | Flooring: Altro Zodiak - Comet |
| | | |
| | 02- | Body & Chassis |
| 1 | STD | This chassis is equipped with a Diesel Exhaust Fluid (DEF) System to meet EPA Diesel Emissions Standards. |
| 1 | STD | Pass-Thru w/ sliding window- Slides behind Passenger's seat |
| 2 | STD | IV Hangers: (2) Cast black rubber fold-down over chest area of stretcher and Squad Bench |
| 3 | STD | Mirrors, OEM: (1) each cab door, (1) on interior windshield |
| 4 | STD | Wheel Covers, OEM |
| 1 | STD | OEM fuel fill behind panel by driver's door |
| 1 | STD | Undercoating: Per OEM Guidelines |
| | | |
| | 03- | Brake, Turn & Back-Up Lights |
| 1 | STD | OEM Standard Stop, Tail and Turn Lights |
| | | |
| | 04- | Electrical, Power Distribution, Control Center & Interior Lighting |
| 1 | STD | Battery Switch, Automatic: Located in Electrical Cabinet. |
| 2 | STD | Antenna, Radios Coax Cable- Terminated behind driver's seat w/Power & Ground for each |
| 8 | STD | Dome Lights: Whelen MX80EHZA 2- Banks of four LED lights switched separately with Hi/Lo functions |
| 1 | STD | Action Area Light: Whelen PSC0ADCR, 12 VDC LED Strip light, 6 diodes and On/Off switch on rear control panel |
| 1 | STD | USB Port: Vanner VSS-USB dual port 2Amp mounted on A/A wall |
| 1 | STD | Shoreline: 125 VAC, 20-amp, 60 HZ, straight blade inlet w/hinged, weatherproof cover. Located on SS behind driver's door. |
| 1 | STD | Timer- 5-minute check-out wired to CS High Dome lights |
| 1 | STD | Pre-Wire for Inverter w/Switch in Rear Panel; Located in lower main cabinet |
| 3 | STD | 12 VDC Outlets- 2 located in Action Area and (1) located in ALS |
| 3 | STD | 125 VAC Outlet- (1) in Action Area, (1) Curbside wall at the head of the squad bench and (1) located in ALS |
| 1 | STD | Breaker Box: 125 VAC w/20-Amp Breaker located behind the lower main access panel. GFI receptacle located on the Action Area wall. |
| 1 | STD | Spotlight, 400,000 CP, handheld, hardwired w/momentary On/Off switch |

| | | |
|---|-----|---|
| 1 | STD | Front Console: Vacu-Formed ABS housing on top of OEM engine cowl w/switch panel angled for visibility. |
| 1 | STD | Electrical Cabinet: Located in upper streetside wall with vented, removable panel |
| 1 | STD | Battery Conditioner, Power Source, 45-Amp- located behind access door in lower base cabinet |
| 05- Warning Lights & Sirens | | |
| 1 | STD | Forward Lighting: (5) Whelen 700 Series Super LEDs, (4)-70R02FCR Red, (1)- 70C02FCR White mounted on custom engineered front facing fairing mounted on the OEM roof above the front windshield. R/R/W/R/R w/chrome bezels |
| 2 | STD | Lights Warning: Whelen 700 Series Super LEDs Red 70R02FCR, (2)- mounted (1)- each on upper rear door corners in Cast bezels. |
| 2 | STD | Lights Warning: Whelen 700 Series Super LEDs Amber 70A02FCR, (2)- mounted (1)- each on upper rear door corners in Cast bezels, inboard of rear emergency flasher. |
| 2 | STD | Lights Warning: 1- M2WRC Red LED mounted each side on the OEM front fenders w/chrome bezels. |
| 2 | STD | Lights Warning: 2 LINZ6R Red LED mounted OEM grille w/chrome bezel. |
| 4 | STD | EMERGENCY/SCENE LIGHTS: (4)- M9RCZ LED combination Emergency and Scene lights mounted at each upper corner of the OEM chassis w/Whelen angled chrome mounting bezel. |
| 2 | STD | Lights Warning, Whelen Micron MCRNSK split Amber/Red LED mounted above the rear entry doors to be visible only when the rear doors are open. |
| 2 | STD | Lights, Load: 2- PELCC LED Load lights mounted on the upper rear corners of the interior door jamb w/chrome bezel |
| 1 | STD | Flasher- for Warning Light system, Vanner 9860GCPE - to be used with the 700 series lights |
| 2 | STD | Siren Speakers: Dual 100 watt Speakers mounted behind the OEM front bumper: CPI SAP3801/SAD3801 |
| 1 | STD | Siren, Whelen 295HFSA7 Dual Tone amplifier 200 Watt |
| 06- Oxygen, Vacuum & Miscellaneous Items | | |
| 3 | STD | Oxygen Outlets: Quick-connect style, 2-in Action Area, 1-over Squad Bench |
| 1 | STD | Electric Oxygen with manual bypass |
| 1 | STD | Suction Aspirator System: Rico disposable container mounted in Action Area w/gauge and quick-connect; GAST vacuum pump mounted in rear air return |
| 1 | STD | Oxygen Cylinder Retention: For "M" cylinder, black steel w/3-spring buckle straps and top collar on slide-out, tilt-down tray w/lift strap; Located transverse at bulkhead. Side entry door access |
| 1 | STD | O2 Regulator: Amvex, 50psi, pre-set |
| 07- AC / Heat | | |
| 1 | STD | High Capacity Up-Draft Heat/AC System ducted thru angled panel between main and upper cabinets. Multi-speed fan and thermostatic control in Action Area; HVAC unit located behind vented access in lower main cabinet wall. |
| 08- Cabinets, Hardware & Miscellaneous Items | | |
| 1 | STD | Main Streetside Cabinet Wall: horizontal back board storage, HVAC access, inverter access, HVAC vents, (2) upper wall cabinet storage and (4) mid-wall w/1 adjustable shelf each |
| 1 | STD | ALS Cabinet: Open Lower, Locking storage for 747 box - middle section, Open upper shelf storage, Lock box cabinet at top of ALS; Both doors to have a Southco Round, Metal Latch each; access thru Curbside Door. |
| | | SO/TD O2 Bracket w/latch and pull strap, accessible through curb side entry door, hinged aluminum door. Head of O2 cylinder accessible through sliding window below tech seat. |
| 1 | STD | Stair Chair Storage, Vertical Slide-in w/single seat belt style restraint strap Bulkhead wall w/access at side entry door. |
| 1 | STD | Backboard Storage: Horizontal slot at street side rear door with space for 16"/18" boards |
| 1 | STD | Cargo Net @ head of squad bench |

| | | |
|--------------------|----------------|--|
| 1 | STD | Squad Bench-Powder Coated Aluminum Exterior, Herculined Interior and Stainless Steel Kickplate on face: |
| | 1 | Full length hinged lid - HDPE |
| | 2 | Full length upholstered seat cushion except over Sharps/Waste Area; formed upholstered back rest cushions and head pad for each seated position. |
| | 3 | (2) EVS V-4 Belted seating positions w/(3) short bottom straps for 2nd Patient restraint |
| | 4 | Sharps/Waste: Drop-in style w/Red polycarbonate hinged lid and standard containers, located at head of squad bench. |
| 1 | STD | Technician's Seat: EVS 1760 seat w/Type II Shoulder/Lap belt mounted on structure around O2 cylinder; front access to O2 cylinder valve |
| 1 | STD | Assist Rail, overhead in center of unit w/radius ends P/N 49-100936 |
| 2 | STD | Grab Handles: one on each rear entry door |
| 1 | STD | Grab Handle: (1) 18" on Streetside cabinetry at rear entry door |
| 1 | STD | Grab Handle: (1) 36" on ALS cabinet to use at side entry door |
| 1 | STD | Glove Box Holder: Three-sized cabinet w/hinged aluminum door; Located above Action Area |
| 4 | STD | Reflective Striping, Door Open Protection: .50" Red reflective striping around interior door pan of all body doors. |
| | | |
| | 09- | Cots & Miscellaneous Items |
| 0 | 99-1196 | Cot Mount: FW 91" Stat Trac without ICS installed in Transit models only |
| | | |
| | 10- | Paint & Lettering |
| 1 | STD | Paint: Body All White |
| | | |
| 1 | 1000100 | Roof Star ONLY, INSTALLED |
| | | |
| | | SHIP LOOSE |
| 2 | STD | 5 Lb. Fire Extinguisher- Ship Loose is Standard |
| | | |
| | | |
| TOTAL ORDER | | |

I have reviewed this Order and find it to be acceptable and ready to build.

_____ **Date:** _____
 Dealer Signature

I have reviewed this Order and find it to be acceptable and ready to build with the addition of the attached, approved changes.

_____ **Date:** _____
 Dealer Signature

Due to on-going product improvements and the changing requirements of the ambulance industry, MEDIX Specialty Vehicles, Inc. reserves the right to change product specifications and related products without prior notice and without any obligation to change prior products or parts. ALL PATENTS RIGHTS RESERVED.