



Unit #: **XX-XXXX**

DEALER: XYZ Dealer
 CUSTOMER: XYZ Emergency Ambulance
 Street or P.O. Box _____
 City, State, Zip _____
 Customer Contact: _____
 Sales Associate: _____
 VIN#: MEDIX will assign VIN

Chassis Model Yr		2017
MEDIX Model		Type III-AD 170- MSV II
CHASSIS		Chevy/GMC 4500 Cutaway, 6.0L Vortec Gasoline, 159" WB, 14,200 GVWR
BODY		170"L x 96"W x 72" Interior Headroom
QTY	STD/OPT	Description
1	15-M2-CD	Chassis & Conversion
		NOTE: This Chevy gas chassis to have 300 Amp alternator ILOS.
	01-	Flooring & Interior Colors
1	STD	Cabinets: Laminated Wood- (Specify Color) Color:
1	STD	Upholstery: (Specify Color & compare to std. countertop color) Color: Brand: EVS
1	STD	EVS Cushions & Corner Padding
1	STD	Flooring: Lonseal- LonPlate (Diamond Plate) (Specify Color) Color:
	02-	Body & Chassis
1	STD	This chassis is equipped with a Gasoline Exhaust System to meet the EPA standards for gasoline exhaust emissions
		M-2 Standard Configuration
1	STD	All Exterior compartments coated with light gray colored rubberized urethan material.
1	STD	Compartment Lights: Optronics ILL36CB LED Compartment lights- ALL Models Locate: (1) Ceiling of Compt #1; (2) in Compt #2- (1) URH, (1) LLH; (1) in ceiling of Compartment #3; (2) in Compt #4/5; (1) in Compt #6.
1	STD	Compartment #1 SS Forward: Smooth Aluminum body, O2 Universal "M" or "H" cylinder storage for STEEL tank, Door w/gas strut hold-open, Sealed access to paddle handle in door panel. Stainless steel sill protector.
1	STD	Compartment #2 SS Center: Smooth Aluminum body, Open Storage, Double doors w/gas strut hold-opens. (1) Adjustable aluminum shelf w/DA finish. Sealed access to paddle handles in door panel. Stainless steel sill protector.
1	STD	Compartment #3 SS Rear: 3/4 Height, Smooth Aluminum body, Inside/Outside access, (1)-adjustable shelf w/DA finish. Door w/gas strut hold-open. Sealed access to paddle handle in door panel, Stainless steel sill protector.
2	STD	Rear Entry Doors: Dual door system w/exterior/interior, locking paddle handles; fixed glass windows and Cast Grabber hold-opens. Sealed access to paddle handles in door panels. Stainless steel sill protector. Two-piece interior door panel.

1	STD	Compartment #4/5 CS Forward: NO body above floor, ALS Cabinet w/Inside/Outside access, Full height, single Door w/gas strut hold-open. Bottom section aluminum body w/roll-out battery tray for (2nd) battery w/removable, latching door. Sealed access to paddle handle in door panel. Stainless steel sill protector.
1	STD	Curbside Entry Door: Single door system w/exterior/interior, locking paddle handles; window w/fixed glass; Gas strut hold-open. Sealed access to paddle handles in door panel. LED Step well light. Stainless steel sill protector. Two-piece interior door panel.
1	STD	Curbside Entry Door Stepwell: One-piece construction; (1) .125" smooth aluminum welded into door opening coated with Herculiner material. Stainless steel threshold trim. Dri-Dek insert on floor.
1	STD	Compartment #6 CS Rear: Smooth Aluminum body, Vertical backboard storage w/(2) seat belts restraints (1) in upper Backboard section, (1) lower across Backboard and Stair Chair Section. Door w/gas strut hold-open. Sealed access to paddle handles in door panel, Stainless steel sill protector.
1	STD	Divider: Aluminum w/DA finish, vertical in back Board Compartment
		Locate: Compartment #6
1	STD	All Entry Door paddle handle and rotary latching components will include emergency door releases located top and bottom of each door and shall meet the FMVSS 206 30G Test Requirement
1	STD	Walk-Thru w/Sliding Door: Slides behind driver's seat, w/positive friction catch, and folding handle. Fluid dam at threshold.
1	STD	Running Boards: Aluminum diamond plate w/splash guards
1	STD	Fender Flares: Stainless Steel
1	STD	Rear Bumper: ADP corner pods w/Dock bumper pads, Center grip-strut flip-up step, powder coated steel frame
2	STD	IV Hangers: (2) Cast black rubber fold-down over knee area of Cot and Squad Bench
2	STD	Mirrors, Velvac, 2020XG for G-series cutaway with 8D8 option, Heated/Remote Deluxe head w/bottom convex, no turns, Black, Kit# 718416
4	STD	Wheel Covers: Stainless steel covers w/Valve Extenders
4	STD	Stone Guards: Lower body corners, ADP
1	STD	Kick Plate, Rear: ADP, below rear doors across to corner posts
1	STD	Rub Rails: C-Channel, tapered ends, Lower Body off-set mount with neoprene spacers.
2	STD	Fuel Fill Housing: Cast aluminum; Cast aluminum fuel fill housing
2	STD	Fuel Fill Scuff Plate: Stainless steel, below fuel fill bezel
1	STD	Undercoating: Per OEM Guidelines
	03-	Brake, Turn & Back-Up Lights
1	STD	Lights: DOT, Brake/Tail, Turn, Back Up: Whelen 600 Series LED. (Package PNs: 60BTTC, 60A00TAR, 60C00VCR) ILOS
1	STD	DOT Marker Lights: Optronics LED, rubber grommet bezels; (7) MCL11CAB Amber- (5) on front of body as Marker lights, (2) side facing on rear extrusions as Turn Signals; (7) MCL11CRB Red- (5) on rear of Body as Marker lights, (2) side facing as Turn Signals.

04-		Electrical, Power Distribution, Control Center & Interior Lighting
1	STD	Battery Switch, Automatic: TST CDR-357. Located in Electrical Cabinet.
2	STD	Batteries: OEM, 650 C.C.A. Locate: (1) Under hood, (1) In roll-out tray in Compartment #4/5
1	99-0549	Delete single Battery Roll-out Tray; Add Double Battery Roll-out Tray, cables, studs, connectors and 3rd OEM 650 C.C.A. Battery for Type III-AD MSV II
1	STD	Front Console/ Switch Panel: Formed ABS body attached to engine cover. Switch panel: Engraved black plastic with (12) LED lighted switches for Emergency Master, Primary/Secondary Modes, Light Bar, Siren/Horn, Left, Rear and Right Floods, Back-Up Alarm, Module Disconnect. Siren mounted in engraved panel below switches.
2	STD	Antenna, Radio Coax Cables: Terminated behind driver's seat w/Power & Ground for each
11	STD	Dome Lights: Whelen Halogen: 2-banks of four (4) lights switched separately with Hi/Lo functions; 1-bank of three (3) lights centered over cot, switched separately with Hi/Lo functions.
1	STD	Action Area Light: Whelen PSC0ADCR, 12 VDC LED Strip light, 6 diodes and On/Off switch on rear control panel
1	STD	USB Port: Vanner VSS-USB dual port 2Amp mounted on A/A wall
1	STD	Shoreline: 125 VAC, 20-Amp, 60 Hz, straight blade inlet w/hinged, weatherproof cover, located above Compartment #2 SS
2	STD	Switch, Momentary Disable: For Scene/Load Lights. (1) Located on Curbside Wall in 4-position plastic bezel: MX01507. (1) Located on Rear Curbside wall in standardized position, no bezel required, vertical S.S. trim is punched for switch.
1	STD	Timer: 5-minute check-out, wired to CS High mode dome lights
1	STD	Inverter: Pre-Wire w/switch on rear panel. Pre-wire located in ceiling of Compartment #2
1	STD	Battery Conditioner: Power Source, 45-Amp- Ceiling of Compartment #2
3	STD	12 VDC Outlets: (1) in Action Area, (1) in ALS Cabinet, (1) in 2nd Action Area
3	STD	125 VAC Outlets: Duplex, located (1) in Action Area, (1) in ALS, (1) in 2nd Action Area
1	STD	Breaker Box: 125 VAC w/20-Amp Breaker located behind the driver's seat base. GFI receptacle located on the Action Area wall.
1	STD	Spotlight: 400,000 CP handheld, hard wired, w/momentary On/Off switch, located in cab
1	STD	Rear Switch Panel: Engraved black plastic panel with (14) LED lighted switch positions for Dome Lights (3), Vacuum (1), Vent (1), A.A. Light (1), Inverter (1), AC/Heat (1), Fan Speed (1), <u>Spare switches</u> , Thermostat <u>and digital clock w/Mode Buttons</u> . MX01516.
1	STD	Electrical Cabinet: Located over walk-thru w/latching, recessed, vented door
05-		Warning Lights & Sirens

1	500114+	Lights; Warning, Whelen LED EMERGENCY Lighting Package- Ford, Chevy <u>Type I and Type III</u>- MSV-II Models ONLY. NOTE: Does not include LED Scene or Load Lights.
		DELETE All standard halogen WARNING Lights.
		All LED lights shall have CLEAR Lenses. All emergency and scene lighting shall have chrome flanges in standard locations.
		<u>Front of Body:</u> Add (7) Whelen 900 Series Super-LEDs- Specify pattern by LED Color (Red or White): _____ Outer (2) lights and (1) Center light flash on K-Spec flasher. Inner (4) flash independently on Light Bar switch on front console.
		<u>Sides of Body:</u> (4) Whelen 900 Series Red Super-LEDs: (2) each side in upper corners
		<u>Rear of Body:</u> (4) Whelen 900 Series Red Super-LEDs: (2) in upper outboard corners, (2) Mid-Body wired as Warning/Brake at the window level; (1) Whelen 900 Series Amber Super-LED in the center position over the rear doors.
		<u>Brake, Turn & Back-Up Lights:</u> Whelen 600 Series LEDs, (60BTT, 60A00TAR, 60C00VCR)
		<u>Lights, Warning, Intersection Lights:</u> (2) Whelen 700 Series Red Super-LEDs on Front Fenders; (2) Whelen 700 Series Red Super-LEDs above rear Wheel Wells- wired to Pri/Sec Modes
2	STD	Lights, Warning, Grille: LINZ6R Red LED w/clear lenses & chrome flanges on center grille bar
4	STD	Lights, Scene: Whelen 900 Series Halogen w/8-32 degree optics, (2) each side
2	STD	Lights, Load: Whelen 900 Series Halogen w/8-32 degree optics, (2) rear
1	STD	Flasher: Dual mode flasher for Warning Light system, Vanner 9860GCPE
2	STD	Siren Speakers: dual 100 Watt drivers mounted through the front bumper
1	STD	Siren- Whelen 295 SLSA1, 200 Watt
		06- Oxygen, Vacuum & Miscellaneous Items
3	STD	Oxygen Outlets: Quick-connect style, 2-in Action Area, 1-over Squad Bench
1	STD	Electric Oxygen with manual bypass and switch on A/A panel
1	STD	Suction Aspirator System: SSCOR disposable container mounted in recess below Action Area, w/SSCOR gauge and quick-connect in recessed area; GAST vacuum pump mounted on ceiling of Compartment #2.
1	STD	Oxygen Cylinder Retention: Universal for "M" or "H" cylinder, steel w/3-spring buckle straps and top collar, powder-coated Safety Yellow color- in Compartment #1.
1	STD	O2 Regulator: Amvex, 50psi, pre-set
		07- AC / Heat
1	STD	HVAC System: High capacity Free Blow combination Heat-AC system, multi-speed fan and thermostatic control in Action Area. HVAC unit mounted in Front bulkhead over Walk-Thru.
		08- Cabinets, Hardware & Miscellaneous Items
1	STD	Main Streetside Wall Cabinets: Specify required configuration-
0	STD	Full Wall of Cabinets

0	OPT	Cabinet Configuration- CPR Seat w/EVS V-4 seat belt system and 2nd Action Area; includes (1) 125VAC and (1) 12VDC outlet in 2nd Action Area
		Main Wall aisle-facing Cabinets will have (1) adjustable laminated wood shelf in each and sliding Lexan doors with full height extruded handles. Recessed cabinet for suction aspirator container. Stainless steel trim on lower face. See Prints for Configuration.
1	STD	Action Area Overhead Cabinet: Full-height and depth aisle-facing cabinet w/sliding Lexan doors and full height extruded handles.
1	STD	Action Area and <u>Switch Panel</u> : Laminated, sealed countertop and vertical panel with Suction system collection cannister, Vacuum gauge, (2) Oxygen outlets, (1) 12VDC Outlet, and (1) 125VAC Outlet. <u>Switch panel includes (14) switch positions, Thermostat and digital clock w/Mode Buttons. MX01516</u>
1	STD	Corian Countertop- 1st / 2nd Action Area, Color: _____ w/ _____ Top and perimeter accent lips. To extend over the edge of cabinet main
1	STD	CPR Seat, 2nd Action Area: CPR seat w/hinged, latching lid, storage under seat w/TriMark latch, EVS formed back rest and seat cushion; 2nd Action Area w/(1) 12VDC outlet, (1) 125VAC outlet
1	STD	Cabinet overhead, rear of CPR Seat: Full-height and depth aisle-facing cabinet w/sliding Lexan doors and full height extruded handles.
1	STD	Sharps/Waste Tilt-Out Cabinet: Below 2nd Action Area w/round SouthCo latch.
1	STD	Inside/Outside access to Compartment #3: With dual 1/2" Acrylic hinged doors w/round SouthCo latches
1	STD	Technician's Seat: EVS Rear facing automotive style chair with Type II lap/shoulder belt mounted on swivel base.
1	STD	Seat Base: EVS SB-2 Swivel Base for EVS Technician's Seat
2	STD	Front Bulkhead Wall Cabinets: Electrical Cabinet located above Tech Seat w/round SouthCo latching, vented door; HVAC cabinet and filtered air return above Walk-Thru.
1	STD	Bulkhead Cabinets: Upper cabinet- open storage w/hinged, round SouthCo latching door; Lower cabinet open storage w/hinged, round SouthCo latching, vented door.
1	STD	Cabinet Above ALS: Open storage w/dual 1/2" Acrylic doors w/non-locking SouthCo round latches, (1) adjustable shelf.
1	STD	ALS Cabinet: Lower Section- Locking storage for box or bags w/LonPlate flooring; Middle Section- 6-inch deep drawer w/locking latch and gas strut closure w/Dri-Dek mat; Upper Section- w/ dual 1/2" Acrylic doors w/round SouthCo latches and (1) adjustable shelf w/ LonPlate flooring.
1	STD	Glove Box Holders: (3) w/hinged, powder-coated steel door, in pad above Curbside Entry Door
1	STD	Squad Bench:
	1	Full length hinged lid w/TriMark latch for access to interior storage
	2	Full length upholstered seat cushion; vacuum formed, upholstered back rest cushions and head pad for each seated position.
	3	(2) EVS V-4 Belted seating positions w/(3) short bottom straps for 2nd Patient restraint
	4	Stainless steel trim on lower face.
1	STD	Sharps/Waste: Drop-in style w/Red polycarbonate hinged lid with standard containers, located at head of squad bench.

1	STD	Cabinet, Squad Bench Overhead: w/ (2) flip-up 1/2" Acrylic doors with round SouthCo latches.
1	STD	Cabinet, Rear Overhead: Cabinet over rear door opening w/ (1) flip-up 1/2" Acrylic door w/round SouthCo latch.
1	STD	Assist Rail: 1.25" Stainless steel w/radiused ends, overhead off-set toward Streetside.
3	STD	Grab handles: 12" x 1.25" dia. stainless steel mounted on each rear entry and curbside entry door
3	STD	Reflective Striping- Alternate Red/White chevron pattern on smooth aluminum kick panel-mounted on each rear entry and curbside entry door
9	STD	Reflective Striping, Door Open Protection: .50" Red reflective striping around interior door pan of all body doors.
	09-	Cots & Miscellaneous Items
0	99-0724	Cot Mount: Select- Ferno 96" Stat Trac installed in center position
	10-	Paint & Lettering
1	STD	Paint: Body all OEM White
1	1000100	Roof Star ONLY, INSTALLED
		SHIP LOOSE
2	STD	Fire Extinguisher: (2) 5 lb- Ship Loose is Standard
TOTAL ORDER		

I have reviewed this Order and find it to be acceptable and ready to build.

_____ **Date:** _____
 Dealer Signature

I have reviewed this Order and find it to be acceptable and ready to build with the addition of the attached, approved changes.

_____ **Date:** _____
 Dealer Signature

Due to on-going product improvements and the changing requirements of the ambulance industry, MEDIX Specialty Vehicles, Inc. reserves the right to change product specifications and related products without prior notice and without any obligation to change prior products or parts. ALL PATENTS RIGHTS RESERVED.