



MSVI Unit #:
XXXXX

DEALER: XYZ Dealer
 CUSTOMER: XYZ Emergency Ambulance
 Street or P.O. Box _____
 City, State, Zip _____
 Customer Contact: _____
 Sales Associate: _____
 VIN#: *To be assigned by MEDIX*

| Chassis Model Yr | 2018 | |
|------------------|---|--|
| MEDIX Model | Metro Express PC-90 Concept, Type III - CS Squad Bench | |
| CHASSIS | Ford E-350 XL Cutaway, 6.8 L V-10 Gas, 138" WB, 11,500 GVWR | |
| BODY | 153"L x 90"W x 68" Interior Headroom | |
| QTY | STD/OPT | Description |
| 1 | 16-PC90-FG | Chassis & Conversion |
| | 01- | Flooring & Interior Colors |
| 1 | STD | Cabinets: Laminated Wood- (Specify Color) Color: STAINLESS STEEL |
| 1 | STD | Upholstery: (Specify Color) Color: _____ Brand: EVS |
| 1 | STD | Flooring: Altro Zodiak - Comet |
| | 02- | Body & Chassis |
| 1 | STD | All Exterior compartments coated with light gray colored rubberized urethane material. |
| 1 | STD | Pass-Thru w/Sliding Window. Slides behind driver's seat |
| 1 | STD | Fender Flares: Black rubber |
| 1 | STD | Compartment Lights: Optronics ILL36CB LED Compartment lights- ALL Models Locate: (1) Ceiling of Compartment #1; (2) in Compartment #2- (1) URH, (1) LLH; (1) in Compartment #3 ULH; (1) in Compartment #6 (center top). |
| 1 | STD | Compartment #1 SS Forward: <u>Smooth Aluminum</u> body, <u>ADP interior door panel</u> , O2 "M" cylinder storage for STEEL tank, Door w/rubber socket/nylon ball hold-open. |
| 1 | STD | Compartment #2 SS Center: <u>Smooth Aluminum</u> body, <u>ADP interior door panel</u> , Open Storage, Door w/gas strut hold-open and Seat Belt Strap. NOTE: Tub will have a formed aluminum tub recessed into the RH wall (above the wheel well) for mounting the suction pump and battery charger or inverter. |
| 1 | STD | Compartment #3 SS Rear: <u>Smooth Aluminum</u> body, <u>ADP interior door panel</u> , Open Storage, Door w/gas strut hold-open and (1) adjustable shelf. |
| 2 | STD | Rear Entry Doors: Single piece HDPE w/stainless steel center access panel for black paddle handles; Smooth Aluminum kick panels with reflective chevrons. |
| 1 | STD | Curbside Forward Entry Door: Single piece HDPE w/stainless steel center access panel for black paddle handles; Smooth Aluminum kick panels with reflective chevron. Gas strut door hold-open. Smooth aluminum stepwell w/Dri-Dek insert. |

| | | |
|---|------------|--|
| 1 | STD | Compartment #6 SS Rear: <u>Smooth Aluminum</u> body, <u>ADP interior door panel</u> , Vertical backboard storage w/2- belts. Door w/gas strut hold open. |
| 1 | STD | All Entry Door paddle handle and rotary latching components will include emergency door releases located top and bottom of each door and shall meet the FMVSS 206 30G Test Requirement |
| 1 | STD | Rear Bumper: ADP corner pods w/Dock bumper pads, Center grip-strut flip-up step, powder coated steel frame |
| 2 | STD | IV Hangers: (2) Cast black rubber fold-down of knee area of Cot and Squad Bench |
| 3 | STD | Mirrors, OEM: (1) each cab door, (1) on interior windshield |
| 1 | OPT | Wheel Covers: Stainless steel covers w/Valve Extenders |
| 4 | STD | Stone Guards, lower body corners, ADP |
| 2 | STD | Running Boards, formed ADP with front splash guards |
| 1 | STD | Rub Rails, C-Channel, tapered ends, Lower Body off-set mount with neoprene spacers. |
| 1 | STD | Cast aluminum fuel fill bezel |
| 1 | STD | Insulation: Spray in place foam, FR 2-Part Spray Foam, CP-1000 Kit 200, applied to curbside entry step well and both rear wheel wells |
| 1 | STD | Undercoating: Per QVM Guidelines |
| | | |
| | 03- | Brake, Turn & Back-Up Lights |
| 1 | STD | Lights: DOT, Brake/Tail, Turn, Back Up: Whelen 600 Series LED. |
| 1 | STD | DOT Marker Lights: TecNiq LED, rubber grommet bezels; (7) S34-AC09-1 Amber- (5) on front of body as Marker lights, (2) side facing on rear extrusions as Turn Signals; (7) S34-RC90-1 Red- (5) on rear of Body as Marker lights, (2) side facing as Turn Signals. |
| | | |
| | 04- | Electrical, Power Distribution, Control Center & Interior Lighting |
| 1 | STD | Batteries: (2) OEM, (1) located under the hood w/200Amp maxi-fuse for module power and (1) located along the curbside frame rail in OEM battery box behind CS entry stepwell. |
| 1 | STD | Battery Switch, Automatic: TST CDR-357. Located in Electrical Cabinet. |
| 1 | STD | Electrical System: Bussman VEC (Vehicle Electrical System) located on the bulkhead wall above the pass through window in locking HDPE cabinet. |
| 2 | STD | Antenna, Radio Coax Cable terminated behind driver's seat w/Power & Ground for each |
| 1 | STD | USB Port: Vanner VSS-USB dual port 2Amp mounted on A/A wall |
| 8 | STD | Dome Light: Whelen LED, 18-diodes w/chrome flange MX80EHZA , switched separately with Hi/Lo functions- ILOS |
| 1 | STD | Camera System: ASA Electronics / VCMS104i - (1) Flush Mount Camera/White, VOM73MM - Rear View Mirror Color Monitor, CEC34 - 32ft. Cable Locate: (1) Camera mounted off lower RH corner of center rear Amber light; Monitor mounted on cab windshield rear view mirror |
| 1 | STD | Action Area Light: Whelen PSC0ADCR, 12 VDC LED Strip light, 6 diodes and On/Off switch on rear control panel |

| | | |
|---|------------|---|
| 1 | STD | Shoreline: 125 VAC, 20-Amp, 60 Hz, straight blade inlet w/hinged, weatherproof cover, located above Compartment #2 SS |
| 0 | 400100 | 125 VAC: Duplex Outlet, IATS Specify Location(s): Surface mount style - Inside the HDPE ALS cabinet, TOP section-Open storage, LH wall at back upper corner (behind door) (reference photo provided) |
| 1 | STD | Timer: 5-minute check-out, wired to CS High mode dome lights |
| 1 | STD | Inverter, Vanner 20-1050CUL- 1000watt w/battery charger and built-in GFI, remote control w/switch in rear panel. Specify Location: outside compartment #2 in offset to RH. |
| 3 | STD | 12 VDC Outlets: (1) in Action Area, (1) On CS wall above forward cabinet and (1) on rear wall above rear CS wall cabinet in HDPE #6 Compartment cover. |
| 0 | 400020 | 12 VDC Receptacle: Cigar style, IATS Specify Location(s): Recessed style- Inside the HDPE ALS cabinet, TOP section-Open storage, LH wall at back upper corner (behind door) (reference photo provided) |
| 3 | STD | 125 VAC Outlets: Duplex, located 1-in Action Area, (1) On CS wall above forward cabinet and (1) on rear wall above the rear CS wall cabinet in HDPE #6 Compartment cover. |
| 1 | STD | Breaker Box: 125 VAC w/20-Amp Breaker located behind the driver's seat base. |
| 1 | STD | Rear Switch Panel: Engraved black plastic panel with (14) LED lighted switch positions for Dome Lights (2), Vacuum (1), Vent (1), A.A. Light (1), Inverter (1), AC/Heat (1), Fan Speed (1), <u>Spare switches</u> , Thermostat and digital clock w/Mode Buttons. MX01516. |
| 1 | STD | Switches, Duplicate on CS Wall: (1) Heat/AC- On/Off; (1) Fan Speed; (1) SS Domes; (1) CS Domes in etched plastic bezel: MX01458 |
| 1 | STD | Front Console: Formed ABS body attached to engine cover. Switch panel with siren panel below |
| 1 | STD | Electrical Cabinet: Located over pass-thru w/latching, recessed, vented door |
| | | |
| | 05- | Warning Lights & Sirens |
| 1 | STD | All LED Light Package- Ford, Chevy Type I-III Models ONLY; NOTE: Does not include LED Scene or Load Lights. |
| | | All LED lights shall have CLEAR Lenses. All emergency and scene lighting shall have chrome flanges in standard locations. |
| | | Front of Body: Add (7) Whelen 900 Series Suprer-LEDs- Specify pattern by LED Color (Red or White: _____ Outer (2) lights and (1) Center light flash on K-Spec flasher. Inner (4) flash independently on Light Bar switch on front console. |
| | | Sides of Body: (4) Whelen 900 Series Red Super-LEDs: (2) each side in upper corners |
| | | Rear of Body: (4) Whelen 900 Series Red Super-LEDs: (2) in upper outboard corners, (2) Mid-Body wired as Warning/Brake at the window level; (1) Whelen 700 Series Amber Super-LED in the center position over the rear doors. |
| | | Brake, Turn & Back-Up Lights: Whelen 600 Series LEDs |

| | | |
|---|-----|--|
| | | Lights, Warning, Intersection Lights: (2) 700 Series Red LEDs on front fenders |
| 2 | STD | Lights, Warning, Grille: LINZ6R Red LED w/clear lenses & chrome flanges on center grille bar |
| 4 | STD | Lights, Scene: 900 Series Halogen w/8-32-degree optics, (2) located each side |
| 2 | STD | Lights, Load: Whelen 700 Series LED 7SC0ENZR, (2) on rear |
| 1 | STD | Flasher- for Warning Light system, Vanner 9860GCPE |
| 2 | STD | Siren Speakers: dual 100 Watt drivers mounted through the front bumper |
| 1 | STD | Siren- Whelen 295 SLSA1, 200 Watt |
| | | |
| | | 06- Oxygen, Vacuum & Miscellaneous Items |
| 3 | STD | Oxygen Outlets: Quick-connect style, 2-in Action Area, 1-on CS wall above forward cabinet in OH cabinet |
| 1 | STD | Suction Aspirator System: Rico disposable container mounted in Action Area w/gauge and quick-connect; GAST vacuum pump mounted in recess area on the right hand side of the #2 compartment tub in recess on slide out tray. |
| 1 | STD | Oxygen Cylinder Retention: For "M" cylinder, black steel w/3-spring buckle straps and top collar, located in Compartment #1 |
| 1 | STD | O2 Regulator, Amvex, 50psi, pre-set |
| | | |
| | | 07- AC / Heat |
| 1 | STD | HVAC System: High capacity Free Blow combination Heat-AC system, multi-speed fan and thermostatic control in Action Area. HVAC unit mounted above compartment #1 and ducted across top of bulkhead wall. |
| | | NOTE: Return air input to be at bottom of Compartment #1 HDPE interior cover w/plenum built into cover for ducting up to the evaporator unit. 2" hose will feed the A/C - Heater output to the blower outlets. |
| | | |
| | | 08- Cabinets, Hardware & Miscellaneous Items |
| 1 | STD | Main Streetside Wall Cabinets: Specify desired configuration- |
| 1 | STD | Full Wall of Cabinets |
| | | Main Wall Cabinets: (4) standard vac-formed HD ABS cabinets w/HD backers will have extruded aluminum window frames w/sliding Lexan doors, full height extruded handles and (1) adjustable shelf w/3/4" lip in each cabinet. See Prints for Configuration. |
| 1 | STD | Action Area Overhead Cabinet: (1) standard vac-formed HD ABS cabinet w/HD backers will have extruded aluminum window frames w/sliding Lexan doors, full height extruded handles and (1) adjustable shelf w/3/4" lip in each cabinet. |
| 1 | STD | Action Area and Switch Panel: HDPE wall panel w/HDPE sealed countertop and vertical panel CNC'd for Suction system collection cannister, Vacuum gauge, (2) Oxygen outlets, (1) 12VDC Outlet and (1) 125VAC Outlet. Switch panel includes (14) switch positions, Thermostat and digital clock w/Mode Buttons. MX01516 |
| 1 | STD | Radio console with map pocket, located on floor behind ABS console between seats - Use Aluminum Add-On P/N: 44-A11380 |
| 1 | STD | Glove Cabinet: HDPE Single glove cabinet mounted at rear of streetside main wall below power vent. |

| | | |
|--------------------|------------|--|
| 1 | STD | Glove Cabinet: HDPE glove cabinet mounted over the curb side entry door with static air vent and O2 receptacle mounted in cabinet above. |
| 1 | STD | ALS Cabinet: HDPE cabinet (PN: 43-A1-2318) mounted on curb side wall aft of curb side entry door. Upper section w/hinged, non-locking latch for 747 storage, lower open storage. |
| 1 | STD | Squad Bench: |
| | 1 | Full length hinged lid w/TriMark latch for access to interior storage |
| | 2 | Full length upholstered seat cushion; formed upholstered back rest cushions and head pad for each seated position. |
| | 3 | (2) EVS V-4 Belted seating positions w/(3) retractors and short bottom straps for 2nd Patient restraint |
| | 4 | Stainless Steel, 6" on face of squad bench. |
| | 5 | Sharps/Waste: tip out at rear of squad bench with waste receptacle and 2 4"x4" sharps containers. |
| 1 | STD | Technician's Seat: EVS Rear facing automotive style chair with V-4 belt system mounted on EVS CBPED/R seat base. |
| 1 | STD | Assist Rail: 72" Powder Coated Safety Yellow SS 1.25" w/Radius Ends |
| 1 | STD | Grab Handles: (3) 12" Powder Coated Safety Yellow 1.25: SS w/Radius Ends, (1) each entry door |
| 1 | STD | Grab Handle: (1) 18", Powder Coated Safety Yellow, 1.25" SS w/Radius Ends PN: G304-49101356PCBY Location: Bulkhead wall inside curbside entry door |
| 7 | STD | Reflective Striping, Door Open Protection: .50" Red reflective striping around interior door pan of all body doors. |
| | | |
| | 09- | Cots & Miscellaneous Items |
| 0 | 99-0724 | Cot Mount: TBD by final purchaser. NOTE: Floor is designed to accommodate all Ferno and Stryker single position mounts. |
| | | |
| | 10- | Paint & Lettering |
| 1 | STD | Paint: Body all OEM White |
| | | |
| 0 | DEL | DELETE Roof Star ONLY |
| | | |
| | | SHIP LOOSE |
| 2 | STD | 5 Lb. Fire Extinguisher- Ship Loose is Standard |
| | | |
| TOTAL ORDER | | |

I have reviewed this Order and find it to be acceptable and ready to build.

_____ Date: _____
Dealer Signature

I have reviewed this Order and find it to be acceptable and ready to build with the addition of the attached, approved changes.

_____ Date: _____
Dealer Signature

Due to on-going product improvements and the changing requirements of the ambulance industry, MEDIX Specialty Vehicles, Inc. reserves the right to change product specifications and related products without prior notice and without any obligation to change prior products or parts. ALL PATENTS RIGHTS RESERVED.